

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268397

Luminaire Tested: P3AS20R709735D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709735D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1586.1 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268397

CATALOG NUMBER: P3AS20R709735D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268397

CATALOG NUMBER: P3AS20R709735D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307037
5°	303345
10°	294584
15°	282113
20°	264250
25°	240086
30°	207374
35°	165273
40°	120368
45°	79140
50°	37082
55°	11431
60°	11052
65°	10637
70°	10130
75°	10675
80°	9976
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 79140 cd/sqm

TEST NUMBER: P1268397

CATALOG NUMBER: P3AS20R709735D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	8.2
10°-20°	347.8	21.9
20°-30°	452.0	28.5
30°-40°	383.6	24.2
40°-50°	197.8	12.5
50°-60°	38.1	2.4
60°-70°	20.7	1.3
70°-80°	12.7	0.8
80°-90°	3.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.6	58.6
0°-40°	1313.1	82.8
0°-60°	1549.1	97.7
0°-90°	1586.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1586.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1400	
5°	1378	130
15°	1243	348
25°	992	452
35°	617	384
45°	255	198
55°	30	38
65°	20	21
75°	13	13
85°	3	4
90°	0	

TEST NUMBER: P1268397

CATALOG NUMBER: P3AS20R709735D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1400.2
2.5°	1395.5
5°	1378.1
7.5°	1352.9
10°	1323.0
12.5°	1285.2
15°	1242.7
17.5°	1190.7
20°	1132.4
22.5°	1066.3
25°	992.3
27.5°	908.8
30°	819.0
32.5°	719.8
35°	617.4
37.5°	516.6
40°	420.5
42.5°	330.8
45°	255.2
47.5°	187.4
50°	108.7
52.5°	47.3
55°	29.9
57.5°	28.4
60°	25.2
62.5°	23.6
65°	20.5
67.5°	18.9
70°	15.8
72.5°	14.2
75°	12.6
77.5°	9.5
80°	7.9
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)