

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268504

Luminaire Tested: P3AS02R129740DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129740DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 243.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268504
CATALOG NUMBER: P3AS02R129740DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268504
 CATALOG NUMBER: P3AS02R129740DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	96	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	92	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	89	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	86	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	83	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	81	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	78	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	76	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	74	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207593
5°	184261
10°	127965
15°	75664
20°	43100
25°	24630
30°	13622
35°	7281
40°	4008
45°	2171
50°	1365
55°	1070
60°	921
65°	830
70°	769
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2171 cd/sqm



TEST NUMBER: P1268504
 CATALOG NUMBER: P3AS02R129740DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.2	29.3
10°-20°	93.9	38.7
20°-30°	48.4	19.9
30°-40°	18.2	7.5
40°-50°	6.0	2.5
50°-60°	2.6	1.0
60°-70°	1.6	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.5	87.9
0°-40°	231.7	95.3
0°-60°	240.2	98.8
0°-90°	243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	243.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	837	71
15°	333	94
25°	102	48
35°	27	18
45°	7	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1268504
CATALOG NUMBER: P3AS02R129740DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	946.7
1°	944.8
2°	932.4
3°	908.7
4°	877.6
5°	837.1
6°	791.2
7°	740.9
8°	685.0
9°	629.7
10°	574.7
12.5°	442.2
15°	333.3
17.5°	249.5
20°	184.7
22.5°	137.9
25°	101.8
27.5°	74.2
30°	53.8
32.5°	38.2
35°	27.2
37.5°	19.4
40°	14.0
42.5°	10.1
45°	7.0
47.5°	5.2
50°	4.0
52.5°	3.3
55°	2.8
57.5°	2.3
60°	2.1
62.5°	1.9
65°	1.6
67.5°	1.4
70°	1.2
72.5°	1.2
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)