

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268515

Luminaire Tested: P3AS02R129740DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129740DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 181.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268515

CATALOG NUMBER: P3AS02R129740DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1268515

CATALOG NUMBER: P3AS02R129740DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	83	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52671
5°	49373
10°	40480
15°	31464
20°	24829
25°	19791
30°	15876
35°	12956
40°	10677
45°	8993
50°	7710
55°	6690
60°	5921
65°	5137
70°	4552
75°	3728
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8993 cd/sqm

TEST NUMBER: P1268515

CATALOG NUMBER: P3AS02R129740DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.0	11.1
10°-20°	38.8	21.4
20°-30°	37.7	20.8
30°-40°	30.5	16.8
40°-50°	22.6	12.5
50°-60°	15.8	8.7
60°-70°	9.9	5.5
70°-80°	4.7	2.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.6	53.3
0°-40°	127.1	70.2
0°-60°	165.5	91.4
0°-90°	181.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	181.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	224	20
15°	139	39
25°	82	38
35°	48	30
45°	29	23
55°	18	16
65°	10	10
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1268515

CATALOG NUMBER: P3AS02R129740DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.2
2.5°	236.2
5°	224.3
7.5°	205.3
10°	181.8
12.5°	158.8
15°	138.6
17.5°	121.5
20°	106.4
22.5°	93.3
25°	81.8
27.5°	71.5
30°	62.7
32.5°	55.2
35°	48.4
37.5°	42.5
40°	37.3
42.5°	33.0
45°	29.0
47.5°	25.8
50°	22.6
52.5°	19.9
55°	17.5
57.5°	15.5
60°	13.5
62.5°	11.5
65°	9.9
67.5°	8.3
70°	7.1
72.5°	5.6
75°	4.4
77.5°	3.2
80°	2.4
82.5°	1.2
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)