

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268521

Luminaire Tested: P3AS02R159740DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159740DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 298.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268521

CATALOG NUMBER: P3AS02R159740DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1268521

CATALOG NUMBER: P3AS02R159740DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	101	108	105	102	100	102	100	98		100	98	97		98
4	107	103	100	97	106	102	99	97	100	97	96		98	96	94		97
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	92	96	93	91		95	92	91		94
7	101	96	92	90	100	95	92	90	94	91	89		93	91	89		92
8	99	94	90	88	98	93	90	88	93	90	88		92	89	87		91
9	97	92	89	87	97	92	89	87	91	88	86		90	88	86		90
10	96	90	87	85	95	90	87	85	89	87	85		89	86	85		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	579230
5°	485471
10°	228675
15°	68945
20°	25506
25°	9920
30°	3697
35°	1124
40°	401
45°	217
50°	171
55°	191
60°	219
65°	104
70°	128
75°	169
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 60°

Luminance: 219 cd/sqm

TEST NUMBER: P1268521

CATALOG NUMBER: P3AS02R159740DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.5	57.2
10°-20°	101.4	34.0
20°-30°	21.3	7.1
30°-40°	3.4	1.1
40°-50°	0.6	0.2
50°-60°	0.4	0.2
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.1	98.4
0°-40°	296.6	99.5
0°-60°	297.6	99.9
0°-90°	298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2642	
5°	2206	171
15°	304	101
25°	41	21
35°	4	3
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268521

CATALOG NUMBER: P3AS02R159740DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2641.5
1°	2633.3
2°	2591.4
3°	2507.5
4°	2384.5
5°	2205.5
6°	1995.1
7°	1754.5
8°	1524.8
9°	1264.7
10°	1027.0
12.5°	554.1
15°	303.7
17.5°	177.9
20°	109.3
22.5°	66.9
25°	41.0
27.5°	24.7
30°	14.6
32.5°	8.2
35°	4.2
37.5°	2.4
40°	1.4
42.5°	0.9
45°	0.7
47.5°	0.5
50°	0.5
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)