

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269337

Luminaire Tested: P3AS09R159740DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159740DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269337
CATALOG NUMBER: P3AS09R159740DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1269337
 CATALOG NUMBER: P3AS09R159740DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	95	93	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	88	85	83	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	82	79	76	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	77	73	70	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	72	68	65	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	68	64	60	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	65	60	57	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	61	57	53	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	58	54	50	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	56	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123521
5°	113405
10°	90357
15°	67537
20°	51291
25°	38833
30°	28739
35°	20532
40°	14055
45°	9830
50°	8358
55°	8220
60°	8508
65°	9028
70°	9168
75°	9489
80°	10355
85°	10315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 12096 cd/sqm



TEST NUMBER: P1269337

CATALOG NUMBER: P3AS09R159740DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	13.8
10°-20°	83.4	25.3
20°-30°	73.9	22.4
30°-40°	48.4	14.7
40°-50°	25.9	7.8
50°-60°	19.5	5.9
60°-70°	16.8	5.1
70°-80°	11.6	3.5
80°-90°	4.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.0	61.5
0°-40°	251.4	76.2
0°-60°	296.8	90.0
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	563	
5°	515	46
15°	298	83
25°	160	74
35°	77	48
45°	32	26
55°	22	20
65°	17	17
75°	11	12
85°	4	5
90°	0	



TEST NUMBER: P1269337
CATALOG NUMBER: P3AS09R159740DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	563.3
2.5°	550.0
5°	515.2
7.5°	464.1
10°	405.8
12.5°	349.6
15°	297.5
17.5°	255.6
20°	219.8
22.5°	188.1
25°	160.5
27.5°	136.0
30°	113.5
32.5°	94.0
35°	76.7
37.5°	61.3
40°	49.1
42.5°	38.8
45°	31.7
47.5°	27.6
50°	24.5
52.5°	23.5
55°	21.5
57.5°	20.4
60°	19.4
62.5°	18.4
65°	17.4
67.5°	15.3
70°	14.3
72.5°	12.3
75°	11.2
77.5°	9.2
80°	8.2
82.5°	7.2
85°	4.1
87.5°	2.0
90°	0.0

(END OF REPORT)