

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268534

Luminaire Tested: P3AS02R159740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 91.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268534

CATALOG NUMBER: P3AS02R159740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268534

CATALOG NUMBER: P3AS02R159740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22959
5°	22320
10°	20396
15°	17866
20°	15331
25°	12799
30°	10255
35°	7683
40°	5582
45°	3659
50°	2286
55°	1529
60°	1360
65°	1245
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3659 cd/sqm

TEST NUMBER: P1268534

CATALOG NUMBER: P3AS02R159740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.4	10.3
10°-20°	21.9	24.1
20°-30°	24.2	26.6
30°-40°	18.1	19.9
40°-50°	9.4	10.3
50°-60°	3.9	4.3
60°-70°	2.4	2.6
70°-80°	1.3	1.5
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	55.5	60.9
0°-40°	73.6	80.9
0°-60°	86.9	95.5
0°-90°	91.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	91.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	105	
5°	101	9
15°	79	22
25°	53	24
35°	29	18
45°	12	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268534

CATALOG NUMBER: P3AS02R159740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	104.7
1°	104.8
2°	104.4
3°	103.8
4°	102.7
5°	101.4
6°	99.8
7°	98.1
8°	96.0
9°	93.8
10°	91.6
12.5°	85.3
15°	78.7
17.5°	72.2
20°	65.7
22.5°	59.1
25°	52.9
27.5°	46.7
30°	40.5
32.5°	34.4
35°	28.7
37.5°	23.9
40°	19.5
42.5°	15.4
45°	11.8
47.5°	8.9
50°	6.7
52.5°	5.0
55°	4.0
57.5°	3.6
60°	3.1
62.5°	2.8
65°	2.4
67.5°	2.1
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)