

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269354

Luminaire Tested: P3AS09R209740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 273.9 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269354
CATALOG NUMBER: P3AS09R209740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269354
 CATALOG NUMBER: P3AS09R209740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67780
5°	65969
10°	60676
15°	53417
20°	45807
25°	38494
30°	31119
35°	23664
40°	16832
45°	11102
50°	6891
55°	4511
60°	4122
65°	3788
70°	3590
75°	3219
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11102 cd/sqm



TEST NUMBER: P1269354
 CATALOG NUMBER: P3AS09R209740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.7	10.1
10°-20°	65.5	23.9
20°-30°	72.7	26.5
30°-40°	55.5	20.2
40°-50°	28.4	10.4
50°-60°	11.7	4.3
60°-70°	7.3	2.7
70°-80°	4.1	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.9	60.6
0°-40°	221.4	80.8
0°-60°	261.4	95.4
0°-90°	273.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	309	
5°	300	28
15°	235	66
25°	159	73
35°	88	55
45°	36	28
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1269354
CATALOG NUMBER: P3AS09R209740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	309.1
1°	309.4
2°	308.0
3°	306.3
4°	303.5
5°	299.7
6°	295.2
7°	290.3
8°	285.1
9°	278.8
10°	272.5
12.5°	254.4
15°	235.3
17.5°	215.8
20°	196.3
22.5°	176.8
25°	159.1
27.5°	141.3
30°	122.9
32.5°	105.5
35°	88.4
37.5°	73.4
40°	58.8
42.5°	46.3
45°	35.8
47.5°	27.1
50°	20.2
52.5°	15.0
55°	11.8
57.5°	10.8
60°	9.4
62.5°	8.4
65°	7.3
67.5°	6.3
70°	5.6
72.5°	4.5
75°	3.8
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3
90°	0.0

(END OF REPORT)