

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268560

Luminaire Tested: P3AS02R209740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 120.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268560

CATALOG NUMBER: P3AS02R209740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268560

CATALOG NUMBER: P3AS02R209740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78
9	86	78	73	70	85	77	73	70	77	73	70		76	72	70		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92317
5°	83931
10°	62034
15°	38366
20°	21912
25°	12509
30°	7014
35°	3828
40°	2090
45°	1147
50°	682
55°	497
60°	439
65°	415
70°	385
75°	424
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1147 cd/sqm

TEST NUMBER: P1268560

CATALOG NUMBER: P3AS02R209740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.0	27.5
10°-20°	47.1	39.3
20°-30°	24.6	20.5
30°-40°	9.5	7.9
40°-50°	3.1	2.6
50°-60°	1.2	1.0
60°-70°	0.8	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.8	87.3
0°-40°	114.3	95.2
0°-60°	118.6	98.8
0°-90°	120.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	120.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	421	
5°	381	33
15°	169	47
25°	52	25
35°	14	10
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268560

CATALOG NUMBER: P3AS02R209740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	421.0
1°	420.2
2°	415.2
3°	407.6
4°	395.8
5°	381.3
6°	364.1
7°	345.1
8°	323.1
9°	301.6
10°	278.6
12.5°	221.4
15°	169.0
17.5°	126.5
20°	93.9
22.5°	69.6
25°	51.7
27.5°	38.1
30°	27.7
32.5°	20.1
35°	14.3
37.5°	10.3
40°	7.3
42.5°	5.2
45°	3.7
47.5°	2.7
50°	2.0
52.5°	1.5
55°	1.3
57.5°	1.2
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.6
75°	0.5
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)