

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268575

Luminaire Tested: P3AS02R259740DE010 E3CB1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R259740DE010 E3CB1MB  
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 300.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268575  
CATALOG NUMBER: P3AS02R259740DE010 E3CB1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1268575  
 CATALOG NUMBER: P3AS02R259740DE010 E3CB1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	320742
5°	297490
10°	230702
15°	115687
20°	38013
25°	15122
30°	5672
35°	1633
40°	744
45°	279
50°	239
55°	191
60°	219
65°	259
70°	128
75°	169
80°	253
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 67.5°  
 Luminance: 287 cd/sqm



TEST NUMBER: P1268575  
 CATALOG NUMBER: P3AS02R259740DE010 E3CB1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.9	39.6
10°-20°	141.8	47.3
20°-30°	32.0	10.7
30°-40°	5.2	1.7
40°-50°	0.9	0.3
50°-60°	0.5	0.2
60°-70°	0.5	0.2
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.7	97.6
0°-40°	297.9	99.3
0°-60°	299.3	99.8
0°-90°	300.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	300.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1463	
5°	1352	119
15°	510	142
25°	62	32
35°	6	5
45°	1	1
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1268575  
CATALOG NUMBER: P3AS02R259740DE010 E3CB1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1462.7
1°	1460.4
2°	1448.6
3°	1426.9
4°	1394.1
5°	1351.5
6°	1300.6
7°	1245.4
8°	1182.2
9°	1113.2
10°	1036.1
11°	947.2
12°	845.0
13°	738.0
14°	623.2
15°	509.6
17.5°	290.4
20°	162.9
22.5°	98.3
25°	62.5
27.5°	38.4
30°	22.4
32.5°	11.8
35°	6.1
37.5°	4.0
40°	2.6
42.5°	1.6
45°	0.9
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1268575  
CATALOG NUMBER: P3AS02R259740DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):



(END OF REPORT)