

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268582

Luminaire Tested: P3AS02R259740DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259740DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 319.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268582

CATALOG NUMBER: P3AS02R259740DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1268582

CATALOG NUMBER: P3AS02R259740DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82
9	93	87	83	81	92	87	83	81	86	83	80	85	82	80	84	82	80
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	349358
5°	323640
10°	250407
15°	119592
20°	39437
25°	16622
30°	6431
35°	2784
40°	916
45°	434
50°	171
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 434 cd/sqm

TEST NUMBER: P1268582

CATALOG NUMBER: P3AS02R259740DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	40.5
10°-20°	147.0	46.1
20°-30°	34.2	10.7
30°-40°	7.2	2.2
40°-50°	1.2	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.4	97.3
0°-40°	317.5	99.6
0°-60°	318.9	100.0
0°-90°	319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1593	
5°	1470	129
15°	527	147
25°	69	34
35°	10	7
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268582

CATALOG NUMBER: P3AS02R259740DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1593.2
1°	1590.0
2°	1573.5
3°	1550.2
4°	1514.7
5°	1470.3
6°	1413.3
7°	1353.6
8°	1286.6
9°	1211.1
10°	1124.6
11°	1024.3
12°	909.2
13°	783.1
14°	651.3
15°	526.8
16°	416.7
17°	324.7
18°	255.4
19°	204.3
20°	169.0
21°	141.2
22°	118.6
23°	99.0
24°	82.8
25°	68.7
27.5°	40.7
30°	25.4
32.5°	16.3
35°	10.4
37.5°	6.2
40°	3.2
42.5°	2.1
45°	1.4
47.5°	0.8
50°	0.5
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0



TEST NUMBER: P1268582

CATALOG NUMBER: P3AS02R259740DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)