

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268591

Luminaire Tested: P3AS02R259740DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259740DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268591

CATALOG NUMBER: P3AS02R259740DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268591

CATALOG NUMBER: P3AS02R259740DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158430
5°	147831
10°	118412
15°	80386
20°	48631
25°	28453
30°	16205
35°	8914
40°	4723
45°	2481
50°	1433
55°	1070
60°	921
65°	986
70°	898
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2481 cd/sqm

TEST NUMBER: P1268591

CATALOG NUMBER: P3AS02R259740DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	24.1
10°-20°	97.3	39.4
20°-30°	55.6	22.5
30°-40°	22.0	8.9
40°-50°	6.7	2.7
50°-60°	2.6	1.1
60°-70°	1.8	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.6	86.1
0°-40°	234.5	95.0
0°-60°	243.9	98.7
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	722	
5°	672	60
15°	354	97
25°	118	56
35°	33	22
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268591

CATALOG NUMBER: P3AS02R259740DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	722.5
1°	721.1
2°	715.2
3°	704.8
4°	690.4
5°	671.6
6°	649.4
7°	624.4
8°	595.3
9°	565.6
10°	531.8
11°	498.5
12°	462.0
13°	425.8
14°	388.8
15°	354.1
17.5°	274.5
20°	208.4
22.5°	156.5
25°	117.6
27.5°	87.1
30°	64.0
32.5°	46.3
35°	33.3
37.5°	23.6
40°	16.5
42.5°	11.3
45°	8.0
47.5°	5.7
50°	4.2
52.5°	3.3
55°	2.8
57.5°	2.6
60°	2.1
62.5°	1.9
65°	1.9
67.5°	1.7
70°	1.4
72.5°	1.2
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1268591

CATALOG NUMBER: P3AS02R259740DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)