

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269434

Luminaire Tested: P3AS09R359740DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359740DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 899.9 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269434
CATALOG NUMBER: P3AS09R359740DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1269434
 CATALOG NUMBER: P3AS09R359740DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78	78	78	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70	70	70	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	586861
5°	574905
10°	534838
15°	392125
20°	200777
25°	72367
30°	28182
35°	9878
40°	4065
45°	1085
50°	955
55°	1070
60°	921
65°	726
70°	898
75°	1186
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 1186 cd/sqm



TEST NUMBER: P1269434
 CATALOG NUMBER: P3AS09R359740DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.5	27.1
10°-20°	456.8	50.8
20°-30°	161.7	18.0
30°-40°	28.3	3.1
40°-50°	4.1	0.5
50°-60°	2.3	0.3
60°-70°	1.6	0.2
70°-80°	1.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.1	95.8
0°-40°	890.4	98.9
0°-60°	896.8	99.7
0°-90°	899.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	899.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2676	
5°	2612	243
15°	1727	457
25°	299	162
35°	37	28
45°	4	4
55°	3	2
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1269434
CATALOG NUMBER: P3AS09R359740DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2676.3
1°	2675.6
2°	2667.1
3°	2650.8
4°	2635.9
5°	2611.8
6°	2587.0
7°	2559.3
8°	2525.3
9°	2472.2
10°	2402.0
11°	2304.9
12°	2188.0
13°	2049.0
14°	1895.9
15°	1727.3
17.5°	1286.4
20°	860.4
22.5°	518.8
25°	299.1
27.5°	178.6
30°	111.3
32.5°	64.5
35°	36.9
37.5°	23.4
40°	14.2
42.5°	7.1
45°	3.5
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.1
60°	2.1
62.5°	2.1
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1269434
CATALOG NUMBER: P3AS09R359740DE010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)