

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268603

Luminaire Tested: P3AS02R259740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 151.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268603

CATALOG NUMBER: P3AS02R259740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268603

CATALOG NUMBER: P3AS02R259740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54820
5°	52586
10°	46069
15°	37026
20°	28446
25°	21534
30°	15547
35°	10333
40°	6269
45°	3659
50°	2320
55°	1873
60°	1667
65°	1453
70°	1218
75°	1186
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3659 cd/sqm

TEST NUMBER: P1268603

CATALOG NUMBER: P3AS02R259740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.7	14.4
10°-20°	45.1	29.9
20°-30°	40.8	27.0
30°-40°	24.5	16.2
40°-50°	9.7	6.4
50°-60°	4.5	3.0
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.6	71.3
0°-40°	132.1	87.5
0°-60°	146.3	96.9
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	250	
5°	239	22
15°	163	45
25°	89	41
35°	39	24
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268603

CATALOG NUMBER: P3AS02R259740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	250.0
1°	250.0
2°	248.8
3°	246.2
4°	242.9
5°	238.9
6°	233.8
7°	227.9
8°	221.0
9°	214.2
10°	206.9
11°	198.5
12°	189.7
13°	181.0
14°	172.3
15°	163.1
17.5°	141.5
20°	121.9
22.5°	104.3
25°	89.0
27.5°	74.6
30°	61.4
32.5°	49.4
35°	38.6
37.5°	29.4
40°	21.9
42.5°	16.0
45°	11.8
47.5°	8.9
50°	6.8
52.5°	5.6
55°	4.9
57.5°	4.2
60°	3.8
62.5°	3.1
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.6
75°	1.4
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1268603

CATALOG NUMBER: P3AS02R259740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)