

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268608

Luminaire Tested: P3AS02R309740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 300.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268608

CATALOG NUMBER: P3AS02R309740DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1268608

CATALOG NUMBER: P3AS02R309740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	100	95	92	89	94	90	88	92	89	87	91	88	87	86	85	84
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81	80	79
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244301
5°	239687
10°	212176
15°	134439
20°	51034
25°	15098
30°	5976
35°	1820
40°	802
45°	279
50°	239
55°	191
60°	219
65°	259
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 279 cd/sqm

TEST NUMBER: P1268608

CATALOG NUMBER: P3AS02R309740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	33.4
10°-20°	156.0	52.0
20°-30°	36.2	12.1
30°-40°	5.6	1.9
40°-50°	0.9	0.3
50°-60°	0.5	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.3	97.5
0°-40°	297.9	99.3
0°-60°	299.3	99.8
0°-90°	300.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	300.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1114	
5°	1089	100
15°	592	156
25°	62	36
35°	7	6
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268608

CATALOG NUMBER: P3AS02R309740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1114.1
1°	1113.4
2°	1110.3
3°	1105.1
4°	1098.5
5°	1088.9
6°	1076.9
7°	1059.0
8°	1034.5
9°	998.4
10°	952.9
11°	894.3
12°	828.0
13°	754.5
14°	673.7
15°	592.2
17.5°	387.4
20°	218.7
22.5°	111.7
25°	62.4
27.5°	38.4
30°	23.6
32.5°	12.7
35°	6.8
37.5°	4.5
40°	2.8
42.5°	1.6
45°	0.9
47.5°	0.7
50°	0.7
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1268608

CATALOG NUMBER: P3AS02R309740DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)