

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268631

Luminaire Tested: P3AS02R309740DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309740DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 152.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268631
CATALOG NUMBER: P3AS02R309740DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1268631
 CATALOG NUMBER: P3AS02R309740DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51948
5°	50319
10°	45334
15°	37503
20°	29029
25°	21775
30°	15825
35°	10547
40°	6469
45°	3814
50°	2320
55°	1873
60°	1667
65°	1349
70°	1218
75°	1186
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3814 cd/sqm



TEST NUMBER: P1268631
 CATALOG NUMBER: P3AS02R309740DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	13.8
10°-20°	45.5	29.9
20°-30°	41.4	27.2
30°-40°	25.0	16.5
40°-50°	10.0	6.6
50°-60°	4.4	2.9
60°-70°	2.7	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.9	71.0
0°-40°	133.0	87.5
0°-60°	147.4	97.0
0°-90°	152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	229	21
15°	165	45
25°	90	41
35°	39	25
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1268631
CATALOG NUMBER: P3AS02R309740DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	236.9
1°	236.6
2°	235.7
3°	234.0
4°	231.7
5°	228.6
6°	224.9
7°	220.8
8°	215.7
9°	209.8
10°	203.6
11°	196.6
12°	189.0
13°	181.5
14°	173.2
15°	165.2
17.5°	144.2
20°	124.4
22.5°	106.1
25°	90.0
27.5°	75.4
30°	62.5
32.5°	50.4
35°	39.4
37.5°	30.2
40°	22.6
42.5°	16.5
45°	12.3
47.5°	9.2
50°	6.8
52.5°	5.4
55°	4.9
57.5°	4.2
60°	3.8
62.5°	3.1
65°	2.6
67.5°	2.4
70°	1.9
72.5°	1.6
75°	1.4
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1268631
CATALOG NUMBER: P3AS02R309740DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)