

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268646

Luminaire Tested: P3AS02R359740DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268646  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359740DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 121.9 lumens  
Efficiency: N/A  
Efficacy: 33.9 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268646  
CATALOG NUMBER: P3AS02R359740DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268646  
 CATALOG NUMBER: P3AS02R359740DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	72	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	61530
5°	59146
10°	51524
15°	39455
20°	26392
25°	15969
30°	9166
35°	5113
40°	2719
45°	1395
50°	682
55°	535
60°	526
65°	415
70°	449
75°	424
80°	379
85°	252

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1395 cd/sqm



TEST NUMBER: P1268646  
 CATALOG NUMBER: P3AS02R359740DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.4	20.0
10°-20°	47.4	38.8
20°-30°	31.0	25.4
30°-40°	12.6	10.3
40°-50°	3.8	3.1
50°-60°	1.3	1.1
60°-70°	0.9	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.8	84.3
0°-40°	115.4	94.6
0°-60°	120.4	98.8
0°-90°	121.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	121.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	281	
5°	269	24
15°	174	47
25°	66	31
35°	19	13
45°	4	4
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1268646  
CATALOG NUMBER: P3AS02R359740DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	280.6
1°	280.1
2°	278.9
3°	276.3
4°	273.3
5°	268.7
6°	262.9
7°	256.4
8°	249.0
9°	240.7
10°	231.4
11°	221.1
12°	210.3
13°	198.2
14°	186.7
15°	173.8
17.5°	142.6
20°	113.1
22.5°	87.0
25°	66.0
27.5°	49.2
30°	36.2
32.5°	26.6
35°	19.1
37.5°	13.6
40°	9.5
42.5°	6.6
45°	4.5
47.5°	3.0
50°	2.0
52.5°	1.5
55°	1.4
57.5°	1.3
60°	1.2
62.5°	1.0
65°	0.8
67.5°	0.7
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1268646  
CATALOG NUMBER: P3AS02R359740DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)