

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268663

Luminaire Tested: P3AS02R359740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 153.0 lumens
Efficiency: N/A
Efficacy: 42.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268663

CATALOG NUMBER: P3AS02R359740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268663

CATALOG NUMBER: P3AS02R359740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49185
5°	47964
10°	43842
15°	37231
20°	29473
25°	22284
30°	16230
35°	10975
40°	6756
45°	3876
50°	2320
55°	1873
60°	1667
65°	1453
70°	1218
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3876 cd/sqm

TEST NUMBER: P1268663

CATALOG NUMBER: P3AS02R359740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.1	13.2
10°-20°	45.2	29.5
20°-30°	42.3	27.6
30°-40°	25.9	16.9
40°-50°	10.2	6.7
50°-60°	4.5	2.9
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.6	70.3
0°-40°	133.5	87.3
0°-60°	148.2	96.9
0°-90°	153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	224	
5°	218	20
15°	164	45
25°	92	42
35°	41	26
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1268663

CATALOG NUMBER: P3AS02R359740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	224.3
1°	224.5
2°	223.8
3°	222.4
4°	220.3
5°	217.9
6°	214.8
7°	211.3
8°	207.1
9°	202.4
10°	196.9
11°	191.3
12°	185.2
13°	178.6
14°	171.3
15°	164.0
17.5°	145.1
20°	126.3
22.5°	108.1
25°	92.1
27.5°	77.3
30°	64.1
32.5°	51.8
35°	41.0
37.5°	31.3
40°	23.6
42.5°	17.0
45°	12.5
47.5°	9.0
50°	6.8
52.5°	5.7
55°	4.9
57.5°	4.2
60°	3.8
62.5°	3.3
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.6
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2



TEST NUMBER: P1268663

CATALOG NUMBER: P3AS02R359740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)