

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269503

Luminaire Tested: P3AS09R459740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269503

CATALOG NUMBER: P3AS09R459740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269503

CATALOG NUMBER: P3AS09R459740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130384
5°	128087
10°	121196
15°	110534
20°	97752
25°	84876
30°	72872
35°	60713
40°	45256
45°	27693
50°	12827
55°	10016
60°	9648
65°	8821
70°	8207
75°	7795
80°	7198
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27693 cd/sqm

TEST NUMBER: P1269503

CATALOG NUMBER: P3AS09R459740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	8.8
10°-20°	135.6	22.0
20°-30°	161.1	26.2
30°-40°	140.0	22.8
40°-50°	70.2	11.4
50°-60°	24.4	4.0
60°-70°	17.1	2.8
70°-80°	9.5	1.6
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.0	57.1
0°-40°	490.9	79.8
0°-60°	585.5	95.2
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	595	
5°	582	54
15°	487	136
25°	351	161
35°	227	140
45°	89	70
55°	26	24
65°	17	17
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1269503

CATALOG NUMBER: P3AS09R459740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	594.6
2.5°	591.8
5°	581.9
7.5°	566.3
10°	544.3
12.5°	517.4
15°	486.9
17.5°	452.9
20°	418.9
22.5°	384.1
25°	350.8
27.5°	318.9
30°	287.8
32.5°	258.0
35°	226.8
37.5°	193.5
40°	158.1
42.5°	123.3
45°	89.3
47.5°	58.8
50°	37.6
52.5°	29.1
55°	26.2
57.5°	24.1
60°	22.0
62.5°	19.8
65°	17.0
67.5°	14.9
70°	12.8
72.5°	10.6
75°	9.2
77.5°	7.1
80°	5.7
82.5°	4.3
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)