

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269509

Luminaire Tested: P3AS09R459740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 510.9 lumens
Efficiency: N/A
Efficacy: 46.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269509

CATALOG NUMBER: P3AS09R459740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269509

CATALOG NUMBER: P3AS09R459740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152203
5°	148734
10°	137205
15°	119297
20°	98009
25°	76262
30°	56312
35°	39618
40°	24732
45°	13397
50°	7232
55°	6232
60°	5570
65°	4774
70°	4103
75°	4236
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13397 cd/sqm

TEST NUMBER: P1269509

CATALOG NUMBER: P3AS09R459740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	12.2
10°-20°	145.3	28.4
20°-30°	144.2	28.2
30°-40°	92.9	18.2
40°-50°	35.8	7.0
50°-60°	14.5	2.8
60°-70°	9.2	1.8
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.1	68.9
0°-40°	445.0	87.1
0°-60°	495.3	96.9
0°-90°	510.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	510.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	676	63
15°	526	145
25°	315	144
35°	148	93
45°	43	36
55°	16	15
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1269509

CATALOG NUMBER: P3AS09R459740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	694.1
2.5°	690.6
5°	675.7
7.5°	650.2
10°	616.2
12.5°	573.7
15°	525.5
17.5°	473.1
20°	420.0
22.5°	366.2
25°	315.2
27.5°	267.0
30°	222.4
32.5°	183.4
35°	148.0
37.5°	116.2
40°	86.4
42.5°	62.3
45°	43.2
47.5°	29.0
50°	21.2
52.5°	17.7
55°	16.3
57.5°	14.2
60°	12.7
62.5°	10.6
65°	9.2
67.5°	7.8
70°	6.4
72.5°	5.7
75°	5.0
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)