

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268742

Luminaire Tested: P3AS02R509740DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509740DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268742

CATALOG NUMBER: P3AS02R509740DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1268742

CATALOG NUMBER: P3AS02R509740DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	102		103	101	99		99	97	96		95	94	93
2	106	100	95	91		103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	92	86	81		97	90	85	81		88	83	79		85	81	78		83	80	77
4	93	85	78	73		91	83	77	73		81	76	72		79	75	71		77	73	70
5	88	78	72	67		86	77	71	66		75	70	66		74	69	65		72	68	64
6	83	73	66	61		81	72	65	61		70	65	60		69	64	60		67	63	59
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	57	52		73	63	56	52		61	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	52	48		56	51	48
10	66	56	49	45		65	55	49	45		54	49	45		54	48	45		53	48	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42058
5°	41448
10°	39612
15°	36686
20°	32973
25°	28986
30°	24637
35°	19997
40°	15000
45°	9675
50°	4605
55°	3632
60°	3421
65°	3165
70°	2885
75°	2626
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9675 cd/sqm

TEST NUMBER: P1268742

CATALOG NUMBER: P3AS02R509740DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.6	8.5
10°-20°	45.1	21.8
20°-30°	54.7	26.4
30°-40°	46.4	22.4
40°-50°	24.1	11.6
50°-60°	8.7	4.2
60°-70°	6.0	2.9
70°-80°	3.3	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	117.4	56.7
0°-40°	163.9	79.1
0°-60°	196.7	95.0
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	192	
5°	188	18
15°	162	45
25°	120	55
35°	75	46
45°	31	24
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1268742

CATALOG NUMBER: P3AS02R509740DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	191.8
2.5°	191.1
5°	188.3
7.5°	184.0
10°	177.9
12.5°	170.1
15°	161.6
17.5°	151.9
20°	141.3
22.5°	130.4
25°	119.8
27.5°	108.7
30°	97.3
32.5°	86.0
35°	74.7
37.5°	63.6
40°	52.4
42.5°	41.8
45°	31.2
47.5°	20.8
50°	13.5
52.5°	10.4
55°	9.5
57.5°	8.5
60°	7.8
62.5°	6.9
65°	6.1
67.5°	5.2
70°	4.5
72.5°	3.8
75°	3.1
77.5°	2.4
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)