

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269579

Luminaire Tested: P3AS09R609740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 365.0 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269579

CATALOG NUMBER: P3AS09R609740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269579

CATALOG NUMBER: P3AS09R609740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86199
5°	85362
10°	82875
15°	77662
20°	68723
25°	57487
30°	45070
35°	32685
40°	21755
45°	13552
50°	7335
55°	2141
60°	1974
65°	1816
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13552 cd/sqm

TEST NUMBER: P1269579

CATALOG NUMBER: P3AS09R609740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.5	10.0
10°-20°	94.9	26.0
20°-30°	108.2	29.6
30°-40°	76.7	21.0
40°-50°	34.8	9.5
50°-60°	7.4	2.0
60°-70°	3.6	1.0
70°-80°	2.2	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.6	65.6
0°-40°	316.3	86.7
0°-60°	358.5	98.2
0°-90°	365.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	365.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	393	
5°	388	37
15°	342	95
25°	238	108
35°	122	77
45°	44	35
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1269579

CATALOG NUMBER: P3AS09R609740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	393.1
2.5°	391.7
5°	387.8
7.5°	381.3
10°	372.2
12.5°	359.4
15°	342.1
17.5°	320.2
20°	294.5
22.5°	266.8
25°	237.6
27.5°	207.8
30°	178.0
32.5°	149.5
35°	122.1
37.5°	97.8
40°	76.0
42.5°	57.6
45°	43.7
47.5°	32.6
50°	21.5
52.5°	10.1
55°	5.6
57.5°	4.9
60°	4.5
62.5°	4.2
65°	3.5
67.5°	3.1
70°	2.8
72.5°	2.4
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)