

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268754

Luminaire Tested: P3AS02R559740DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559740DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 314.0 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268754

CATALOG NUMBER: P3AS02R559740DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1268754

CATALOG NUMBER: P3AS02R559740DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89		
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84		
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79		
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74		
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70		
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66		
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87098
5°	86286
10°	89756
15°	88491
20°	81604
25°	66391
30°	40335
35°	13974
40°	3979
45°	1892
50°	819
55°	344
60°	395
65°	363
70°	321
75°	424
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1892 cd/sqm

TEST NUMBER: P1268754

CATALOG NUMBER: P3AS02R559740DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.9	12.1
10°-20°	108.3	34.5
20°-30°	120.8	38.5
30°-40°	39.5	12.6
40°-50°	5.2	1.7
50°-60°	1.1	0.3
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.0	85.1
0°-40°	306.5	97.6
0°-60°	312.8	99.6
0°-90°	314.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	314.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	397	
5°	392	38
15°	390	108
25°	274	121
35°	52	40
45°	6	5
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268754

CATALOG NUMBER: P3AS02R559740DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	397.2
2.5°	394.3
5°	392.0
7.5°	397.6
10°	403.1
12.5°	400.2
15°	389.8
17.5°	373.3
20°	349.7
22.5°	317.2
25°	274.4
27.5°	220.2
30°	159.3
32.5°	97.7
35°	52.2
37.5°	26.4
40°	13.9
42.5°	9.0
45°	6.1
47.5°	4.2
50°	2.4
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.7
65°	0.7
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)