

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268767

Luminaire Tested: P3AS02R559740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 98.0 lumens
Efficiency: N/A
Efficacy: 27.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268767

CATALOG NUMBER: P3AS02R559740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268767

CATALOG NUMBER: P3AS02R559740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18420
5°	18182
10°	17479
15°	16345
20°	14911
25°	13307
30°	11647
35°	9664
40°	7614
45°	5179
50°	3173
55°	1644
60°	1535
65°	1453
70°	1346
75°	1186
80°	1137
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5179 cd/sqm

TEST NUMBER: P1268767

CATALOG NUMBER: P3AS02R559740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.8	7.9
10°-20°	20.1	20.5
20°-30°	25.2	25.7
30°-40°	22.5	23.0
40°-50°	13.2	13.4
50°-60°	4.6	4.6
60°-70°	2.7	2.8
70°-80°	1.5	1.6
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.1	54.2
0°-40°	75.6	77.1
0°-60°	93.3	95.2
0°-90°	98.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	98.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	84	
5°	83	8
15°	72	20
25°	55	25
35°	36	23
45°	17	13
55°	4	5
65°	3	3
75°	1	2
85°	0	0
90°	0	

TEST NUMBER: P1268767

CATALOG NUMBER: P3AS02R559740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	84.0
2.5°	83.6
5°	82.6
7.5°	80.8
10°	78.5
12.5°	75.6
15°	72.0
17.5°	68.2
20°	63.9
22.5°	59.5
25°	55.0
27.5°	50.5
30°	46.0
32.5°	41.1
35°	36.1
37.5°	31.3
40°	26.6
42.5°	21.6
45°	16.7
47.5°	12.7
50°	9.3
52.5°	6.0
55°	4.3
57.5°	3.8
60°	3.5
62.5°	3.1
65°	2.8
67.5°	2.4
70°	2.1
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)