

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269636

Luminaire Tested: P3AS09R709740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.9 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269636

CATALOG NUMBER: P3AS09R709740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269636

CATALOG NUMBER: P3AS09R709740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	82	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164504
5°	155117
10°	147069
15°	144428
20°	139219
25°	131233
30°	130299
35°	113475
40°	73395
45°	34701
50°	4844
55°	382
60°	307
65°	363
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34701 cd/sqm

TEST NUMBER: P1269636

CATALOG NUMBER: P3AS09R709740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.8	7.8
10°-20°	178.7	21.1
20°-30°	252.8	29.9
30°-40°	254.0	30.0
40°-50°	91.3	10.8
50°-60°	2.4	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	497.2	58.8
0°-40°	751.2	88.8
0°-60°	845.0	99.9
0°-90°	845.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	750	
5°	705	66
15°	636	179
25°	542	253
35°	424	254
45°	112	91
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1269636

CATALOG NUMBER: P3AS09R709740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	750.2
1°	748.1
2°	741.5
3°	731.1
4°	717.9
5°	704.7
6°	692.1
7°	682.4
8°	673.7
9°	666.8
10°	660.5
11°	655.3
12°	650.5
13°	645.6
14°	641.1
15°	636.2
16°	630.3
17°	624.0
18°	616.4
19°	607.0
20°	596.6
21°	585.1
22°	573.7
23°	562.5
24°	551.8
25°	542.4
26°	535.8
27°	530.6
28°	526.4
29°	521.5
30°	514.6
31°	504.5
32°	490.3
32.5°	482.3
33°	471.5
34°	450.3
35°	423.9
36°	394.7
37°	361.7
37.5°	346.4
38°	325.6
39°	288.4
40°	256.4
42.5°	177.6
45°	111.9



TEST NUMBER: P1269636

CATALOG NUMBER: P3AS09R709740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	60.1
50°	14.2
52.5°	1.7
55°	1.0
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)