

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268796

Luminaire Tested: P3AS02R609740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 95.0 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268796

CATALOG NUMBER: P3AS02R609740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268796

CATALOG NUMBER: P3AS02R609740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16863
5°	16685
10°	16099
15°	15210
20°	14025
25°	12702
30°	11268
35°	9637
40°	7643
45°	5396
50°	3241
55°	1644
60°	1579
65°	1453
70°	1346
75°	1271
80°	1137
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5396 cd/sqm

TEST NUMBER: P1268796

CATALOG NUMBER: P3AS02R609740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.1	7.5
10°-20°	18.7	19.7
20°-30°	24.0	25.3
30°-40°	22.3	23.5
40°-50°	13.6	14.3
50°-60°	4.5	4.8
60°-70°	2.8	2.9
70°-80°	1.6	1.6
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	49.9	52.5
0°-40°	72.2	76.0
0°-60°	90.3	95.0
0°-90°	95.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	95.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	77	
5°	76	7
15°	67	19
25°	52	24
35°	36	22
45°	17	14
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1268796

CATALOG NUMBER: P3AS02R609740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	76.9
2.5°	76.6
5°	75.8
7.5°	74.3
10°	72.3
12.5°	69.9
15°	67.0
17.5°	63.6
20°	60.1
22.5°	56.3
25°	52.5
27.5°	48.5
30°	44.5
32.5°	40.5
35°	36.0
37.5°	31.2
40°	26.7
42.5°	22.0
45°	17.4
47.5°	13.5
50°	9.5
52.5°	5.6
55°	4.3
57.5°	3.9
60°	3.6
62.5°	3.1
65°	2.8
67.5°	2.4
70°	2.1
72.5°	1.7
75°	1.5
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)