

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269643

Luminaire Tested: P3AS09R709740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 250.0 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269643

CATALOG NUMBER: P3AS09R709740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269643

CATALOG NUMBER: P3AS09R709740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58636
5°	57561
10°	54285
15°	49262
20°	43100
25°	36341
30°	29751
35°	23075
40°	16517
45°	10451
50°	5219
55°	3173
60°	2763
65°	2542
70°	2244
75°	2033
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10451 cd/sqm

TEST NUMBER: P1269643

CATALOG NUMBER: P3AS09R709740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	9.8
10°-20°	60.4	24.2
20°-30°	68.8	27.5
30°-40°	53.7	21.5
40°-50°	26.4	10.6
50°-60°	8.1	3.2
60°-70°	4.8	1.9
70°-80°	2.6	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.5	61.4
0°-40°	207.3	82.9
0°-60°	241.8	96.7
0°-90°	250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	250.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	267	
5°	262	24
15°	217	60
25°	150	69
35°	86	54
45°	34	26
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1269643

CATALOG NUMBER: P3AS09R709740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	267.4
2.5°	266.0
5°	261.5
7.5°	254.2
10°	243.8
12.5°	231.6
15°	217.0
17.5°	201.3
20°	184.7
22.5°	167.3
25°	150.2
27.5°	133.5
30°	117.5
32.5°	101.5
35°	86.2
37.5°	71.6
40°	57.7
42.5°	44.9
45°	33.7
47.5°	23.6
50°	15.3
52.5°	10.1
55°	8.3
57.5°	7.3
60°	6.3
62.5°	5.6
65°	4.9
67.5°	4.2
70°	3.5
72.5°	2.8
75°	2.4
77.5°	2.1
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)