

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269683

Luminaire Tested: P3AS10R129740DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269683  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS10R129740DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 368.0 lumens  
Efficiency: N/A  
Efficacy: 31.5 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269683  
CATALOG NUMBER: P3AS10R129740DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1269683  
 CATALOG NUMBER: P3AS10R129740DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	137730
5°	126458
10°	100777
15°	75301
20°	57195
25°	43309
30°	32030
35°	22888
40°	15658
45°	10947
50°	9347
55°	9137
60°	9517
65°	10066
70°	10258
75°	10590
80°	11491
85°	11573

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 13440 cd/sqm



TEST NUMBER: P1269683  
 CATALOG NUMBER: P3AS10R129740DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	13.8
10°-20°	93.0	25.3
20°-30°	82.4	22.4
30°-40°	54.0	14.7
40°-50°	28.8	7.8
50°-60°	21.8	5.9
60°-70°	18.8	5.1
70°-80°	12.9	3.5
80°-90°	5.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.4	61.5
0°-40°	280.4	76.2
0°-60°	331.0	89.9
0°-90°	368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	368.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	628	
5°	574	51
15°	332	93
25°	179	82
35°	86	54
45°	35	29
55°	24	22
65°	19	19
75°	12	13
85°	5	5
90°	0	



TEST NUMBER: P1269683  
CATALOG NUMBER: P3AS10R129740DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	628.1
2.5°	613.3
5°	574.5
7.5°	517.5
10°	452.6
12.5°	389.9
15°	331.7
17.5°	285.0
20°	245.1
22.5°	209.8
25°	179.0
27.5°	151.6
30°	126.5
32.5°	104.9
35°	85.5
37.5°	68.4
40°	54.7
42.5°	43.3
45°	35.3
47.5°	30.8
50°	27.4
52.5°	26.2
55°	23.9
57.5°	22.8
60°	21.7
62.5°	20.5
65°	19.4
67.5°	17.1
70°	16.0
72.5°	13.7
75°	12.5
77.5°	10.3
80°	9.1
82.5°	8.0
85°	4.6
87.5°	2.3
90°	0.0

(END OF REPORT)