

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268825

Luminaire Tested: P3AS02R659740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 91.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268825

CATALOG NUMBER: P3AS02R659740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268825

CATALOG NUMBER: P3AS02R659740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16183
5°	15981
10°	15431
15°	14552
20°	13441
25°	12194
30°	10786
35°	9182
40°	7299
45°	5148
50°	3002
55°	1644
60°	1535
65°	1401
70°	1282
75°	1186
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5148 cd/sqm

TEST NUMBER: P1268825

CATALOG NUMBER: P3AS02R659740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.8	7.5
10°-20°	17.9	19.7
20°-30°	23.1	25.4
30°-40°	21.3	23.4
40°-50°	12.9	14.1
50°-60°	4.4	4.8
60°-70°	2.7	2.9
70°-80°	1.5	1.7
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	47.8	52.6
0°-40°	69.1	76.0
0°-60°	86.4	95.0
0°-90°	91.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	91.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	74	
5°	73	7
15°	64	18
25°	50	23
35°	34	21
45°	17	13
55°	4	4
65°	3	3
75°	1	2
85°	0	0
90°	0	

TEST NUMBER: P1268825

CATALOG NUMBER: P3AS02R659740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	73.8
2.5°	73.5
5°	72.6
7.5°	71.2
10°	69.3
12.5°	67.0
15°	64.1
17.5°	61.0
20°	57.6
22.5°	54.0
25°	50.4
27.5°	46.6
30°	42.6
32.5°	38.7
35°	34.3
37.5°	30.0
40°	25.5
42.5°	21.0
45°	16.6
47.5°	12.6
50°	8.8
52.5°	5.5
55°	4.3
57.5°	3.8
60°	3.5
62.5°	3.0
65°	2.7
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)