

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268853

Luminaire Tested: P3AS02R709740DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268853  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709740DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 238.0 lumens  
Efficiency: N/A  
Efficacy: 66.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268853  
CATALOG NUMBER: P3AS02R709740DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268853  
 CATALOG NUMBER: P3AS02R709740DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77			77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70			70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46071
5°	45520
10°	44199
15°	42338
20°	39647
25°	36026
30°	31119
35°	24815
40°	18062
45°	11877
50°	5561
55°	1720
60°	1667
65°	1608
70°	1539
75°	1610
80°	1515
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11877 cd/sqm



TEST NUMBER: P1268853  
 CATALOG NUMBER: P3AS02R709740DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.5	8.2
10°-20°	52.2	21.9
20°-30°	67.8	28.5
30°-40°	57.6	24.2
40°-50°	29.7	12.5
50°-60°	5.7	2.4
60°-70°	3.1	1.3
70°-80°	1.9	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.5	58.6
0°-40°	197.1	82.8
0°-60°	232.5	97.7
0°-90°	238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	238.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	210	
5°	207	19
15°	186	52
25°	149	68
35°	93	58
45°	38	30
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1268853  
CATALOG NUMBER: P3AS02R709740DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	210.1
2.5°	209.4
5°	206.8
7.5°	203.0
10°	198.5
12.5°	192.9
15°	186.5
17.5°	178.7
20°	169.9
22.5°	160.0
25°	148.9
27.5°	136.4
30°	122.9
32.5°	108.0
35°	92.7
37.5°	77.5
40°	63.1
42.5°	49.6
45°	38.3
47.5°	28.1
50°	16.3
52.5°	7.1
55°	4.5
57.5°	4.3
60°	3.8
62.5°	3.5
65°	3.1
67.5°	2.8
70°	2.4
72.5°	2.1
75°	1.9
77.5°	1.4
80°	1.2
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)