

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269765

Luminaire Tested: P3AS13R209740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 363.0 lumens
Efficiency: N/A
Efficacy: 24.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269765

CATALOG NUMBER: P3AS13R209740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269765

CATALOG NUMBER: P3AS13R209740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89795
5°	87387
10°	80404
15°	70761
20°	60695
25°	50979
30°	41222
35°	31347
40°	22299
45°	14730
50°	9108
55°	6002
60°	5482
65°	5033
70°	4744
75°	4321
80°	4041
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14730 cd/sqm

TEST NUMBER: P1269765

CATALOG NUMBER: P3AS13R209740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	10.1
10°-20°	86.8	23.9
20°-30°	96.3	26.5
30°-40°	73.5	20.2
40°-50°	37.6	10.4
50°-60°	15.5	4.3
60°-70°	9.7	2.7
70°-80°	5.4	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	219.8	60.6
0°-40°	293.3	80.8
0°-60°	346.4	95.4
0°-90°	363.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	363.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	410	
5°	397	37
15°	312	87
25°	211	96
35°	117	73
45°	48	38
55°	16	15
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1269765

CATALOG NUMBER: P3AS13R209740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	409.5
1°	409.9
2°	408.1
3°	405.8
4°	402.1
5°	397.0
6°	391.0
7°	384.6
8°	377.7
9°	369.4
10°	361.1
12.5°	337.1
15°	311.7
17.5°	285.9
20°	260.1
22.5°	234.2
25°	210.7
27.5°	187.2
30°	162.8
32.5°	139.7
35°	117.1
37.5°	97.3
40°	77.9
42.5°	61.3
45°	47.5
47.5°	36.0
50°	26.7
52.5°	19.8
55°	15.7
57.5°	14.3
60°	12.5
62.5°	11.1
65°	9.7
67.5°	8.3
70°	7.4
72.5°	6.0
75°	5.1
77.5°	4.2
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.5
90°	0.0

(END OF REPORT)