

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269801

Luminaire Tested: P3AS13R259740DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269801
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259740DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.9 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269801

CATALOG NUMBER: P3AS13R259740DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1269801

CATALOG NUMBER: P3AS13R259740DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219281
5°	210389
10°	184299
15°	148151
20°	113830
25°	86110
30°	62237
35°	41332
40°	25076
45°	14606
50°	9313
55°	7570
60°	6622
65°	5863
70°	4809
75°	4745
80°	3536
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14606 cd/sqm

TEST NUMBER: P1269801

CATALOG NUMBER: P3AS13R259740DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	14.4
10°-20°	180.5	29.9
20°-30°	163.2	27.0
30°-40°	98.0	16.2
40°-50°	38.9	6.4
50°-60°	18.0	3.0
60°-70°	10.9	1.8
70°-80°	5.8	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.6	71.3
0°-40°	528.7	87.5
0°-60°	585.5	97.0
0°-90°	603.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1000	
5°	956	87
15°	653	180
25°	356	163
35°	154	98
45°	47	39
55°	20	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1269801

CATALOG NUMBER: P3AS13R259740DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1000.0
1°	1000.0
2°	995.3
3°	985.0
4°	971.8
5°	955.8
6°	935.0
7°	911.5
8°	884.2
9°	856.9
10°	827.7
11°	793.8
12°	759.0
13°	724.1
14°	689.3
15°	652.6
17.5°	565.9
20°	487.8
22.5°	417.1
25°	355.9
27.5°	298.5
30°	245.8
32.5°	197.7
35°	154.4
37.5°	117.7
40°	87.6
42.5°	64.0
45°	47.1
47.5°	35.8
50°	27.3
52.5°	22.6
55°	19.8
57.5°	16.9
60°	15.1
62.5°	12.2
65°	11.3
67.5°	9.4
70°	7.5
72.5°	6.6
75°	5.6
77.5°	4.7
80°	2.8
82.5°	1.9
85°	1.9
87.5°	0.9



TEST NUMBER: P1269801
CATALOG NUMBER: P3AS13R259740DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)