

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268949

Luminaire Tested: P3AS05R159740DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159740DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 383.0 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268949
CATALOG NUMBER: P3AS05R159740DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1268949
 CATALOG NUMBER: P3AS05R159740DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	10.3
10°-20°	92.3	24.1
20°-30°	101.7	26.6
30°-40°	76.2	19.9
40°-50°	39.5	10.3
50°-60°	16.4	4.3
60°-70°	10.1	2.6
70°-80°	5.7	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.5	61.0
0°-40°	309.6	80.9
0°-60°	365.5	95.4
0°-90°	383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	441	
5°	427	39
15°	331	92
25°	223	102
35°	121	76
45°	50	39
55°	17	16
65°	10	10
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1268949
CATALOG NUMBER: P3AS05R159740DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	440.6
1°	441.0
2°	439.6
3°	436.7
4°	432.3
5°	427.0
6°	420.2
7°	412.9
8°	404.2
9°	395.0
10°	385.7
12.5°	359.0
15°	331.4
17.5°	303.7
20°	276.6
22.5°	248.9
25°	222.7
27.5°	196.5
30°	170.3
32.5°	144.6
35°	120.8
37.5°	100.4
40°	82.0
42.5°	65.0
45°	49.5
47.5°	37.4
50°	28.1
52.5°	20.9
55°	17.0
57.5°	15.0
60°	13.1
62.5°	11.6
65°	10.2
67.5°	8.7
70°	7.8
72.5°	6.3
75°	5.3
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)