

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268974

Luminaire Tested: P3AS05R209740DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209740DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 502.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268974
CATALOG NUMBER: P3AS05R209740DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268974

CATALOG NUMBER: P3AS05R209740DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	386241
5°	351089
10°	259470
15°	160523
20°	91661
25°	52334
30°	29346
35°	15954
40°	8759
45°	4807
50°	2797
55°	2026
60°	1930
65°	1764
70°	1539
75°	1610
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4807 cd/sqm



TEST NUMBER: P1268974
 CATALOG NUMBER: P3AS05R209740DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	27.5
10°-20°	197.2	39.3
20°-30°	102.9	20.5
30°-40°	39.8	7.9
40°-50°	12.9	2.6
50°-60°	5.1	1.0
60°-70°	3.4	0.7
70°-80°	2.0	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.2	87.3
0°-40°	478.0	95.2
0°-60°	496.0	98.8
0°-90°	502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1761	
5°	1595	138
15°	707	197
25°	216	103
35°	60	40
45°	16	13
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1268974
CATALOG NUMBER: P3AS05R209740DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1761.4
1°	1758.0
2°	1737.1
3°	1705.1
4°	1655.6
5°	1595.0
6°	1523.2
7°	1443.7
8°	1351.6
9°	1261.9
10°	1165.3
12.5°	926.3
15°	707.1
17.5°	529.1
20°	392.8
22.5°	291.0
25°	216.3
27.5°	159.6
30°	115.9
32.5°	83.9
35°	59.6
37.5°	43.2
40°	30.6
42.5°	21.8
45°	15.5
47.5°	11.2
50°	8.2
52.5°	6.3
55°	5.3
57.5°	4.8
60°	4.4
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	2.4
75°	1.9
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)