

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268999

Luminaire Tested: P3AS05R259740DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259740DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 508.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268999
CATALOG NUMBER: P3AS05R259740DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1268999
 CATALOG NUMBER: P3AS05R259740DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325873
5°	304027
10°	243549
15°	165313
20°	100039
25°	58503
30°	33322
35°	18337
40°	9733
45°	5117
50°	2968
55°	2217
60°	1930
65°	2024
70°	1859
75°	1610
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5117 cd/sqm



TEST NUMBER: P1268999
 CATALOG NUMBER: P3AS05R259740DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.6	24.1
10°-20°	200.2	39.4
20°-30°	114.4	22.5
30°-40°	45.2	8.9
40°-50°	13.8	2.7
50°-60°	5.5	1.1
60°-70°	3.7	0.7
70°-80°	2.0	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.2	86.1
0°-40°	482.3	94.9
0°-60°	501.6	98.7
0°-90°	508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	508.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1486	
5°	1381	123
15°	728	200
25°	242	114
35°	68	45
45°	16	14
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1268999
CATALOG NUMBER: P3AS05R259740DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1486.1
1°	1483.1
2°	1471.0
3°	1449.6
4°	1420.0
5°	1381.2
6°	1335.6
7°	1284.1
8°	1224.4
9°	1163.2
10°	1093.8
11°	1025.3
12°	950.1
13°	875.8
14°	799.6
15°	728.2
17.5°	564.6
20°	428.7
22.5°	321.9
25°	241.8
27.5°	179.1
30°	131.6
32.5°	95.2
35°	68.5
37.5°	48.5
40°	34.0
42.5°	23.3
45°	16.5
47.5°	11.7
50°	8.7
52.5°	6.8
55°	5.8
57.5°	5.3
60°	4.4
62.5°	3.9
65°	3.9
67.5°	3.4
70°	2.9
72.5°	2.4
75°	1.9
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1268999
CATALOG NUMBER: P3AS05R259740DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)