

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269895

Luminaire Tested: P3AS13R409740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 692.0 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269895

CATALOG NUMBER: P3AS13R409740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269895

CATALOG NUMBER: P3AS13R409740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215465
5°	211115
10°	196567
15°	171306
20°	138075
25°	103482
30°	72745
35°	47676
40°	28854
45°	17242
50°	10268
55°	8296
60°	7456
65°	6330
70°	6027
75°	4829
80°	4799
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17242 cd/sqm

TEST NUMBER: P1269895

CATALOG NUMBER: P3AS13R409740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.1	12.9
10°-20°	207.9	30.0
20°-30°	195.9	28.3
30°-40°	113.3	16.4
40°-50°	45.1	6.5
50°-60°	20.0	2.9
60°-70°	12.3	1.8
70°-80°	6.5	0.9
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.8	71.2
0°-40°	606.0	87.6
0°-60°	671.1	97.0
0°-90°	692.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	692.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	983	
5°	959	89
15°	755	208
25°	428	196
35°	178	113
45°	56	45
55°	22	20
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1269895

CATALOG NUMBER: P3AS13R409740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	982.6
2.5°	977.0
5°	959.1
7.5°	926.1
10°	882.8
12.5°	824.4
15°	754.6
17.5°	676.4
20°	591.7
22.5°	506.9
25°	427.7
27.5°	354.2
30°	287.3
32.5°	228.9
35°	178.1
37.5°	134.7
40°	100.8
42.5°	75.4
45°	55.6
47.5°	40.5
50°	30.1
52.5°	24.5
55°	21.7
57.5°	19.8
60°	17.0
62.5°	14.1
65°	12.2
67.5°	10.4
70°	9.4
72.5°	7.5
75°	5.7
77.5°	4.7
80°	3.8
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)