

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269049

Luminaire Tested: P3AS05R309740DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309740DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 37.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269049

CATALOG NUMBER: P3AS05R309740DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1269049

CATALOG NUMBER: P3AS05R309740DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	66	76	70	66		74	69	65		72
6	83	73	67	62	82	72	66	62	71	65	61		69	64	61		68
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	58	52	48	57	51	48		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88633
5°	83579
10°	71453
15°	57253
20°	44641
25°	33558
30°	24485
35°	17266
40°	11822
45°	8466
50°	6925
55°	6690
60°	6754
65°	6901
70°	7181
75°	7710
80°	7956
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 9408 cd/sqm

TEST NUMBER: P1269049

CATALOG NUMBER: P3AS05R309740DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.4	12.6
10°-20°	70.1	25.7
20°-30°	63.9	23.4
30°-40°	40.6	14.9
40°-50°	21.7	8.0
50°-60°	15.9	5.8
60°-70°	13.3	4.9
70°-80°	9.3	3.4
80°-90°	3.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.3	61.7
0°-40°	208.9	76.5
0°-60°	246.6	90.3
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	380	34
15°	252	70
25°	139	64
35°	64	41
45°	27	22
55°	18	16
65°	13	13
75°	9	9
85°	4	4
90°	0	

TEST NUMBER: P1269049

CATALOG NUMBER: P3AS05R309740DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	404.2
2.5°	397.9
5°	379.7
7.5°	353.1
10°	320.9
12.5°	286.5
15°	252.2
17.5°	220.7
20°	191.3
22.5°	163.9
25°	138.7
27.5°	116.3
30°	96.7
32.5°	78.5
35°	64.5
37.5°	51.1
40°	41.3
42.5°	32.9
45°	27.3
47.5°	22.4
50°	20.3
52.5°	18.9
55°	17.5
57.5°	16.8
60°	15.4
62.5°	14.7
65°	13.3
67.5°	12.6
70°	11.2
72.5°	9.8
75°	9.1
77.5°	7.7
80°	6.3
82.5°	5.6
85°	3.5
87.5°	1.4
90°	0.0

(END OF REPORT)