

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269074

Luminaire Tested: P3AS05R359740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 315.0 lumens
Efficiency: N/A
Efficacy: 43.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269074
CATALOG NUMBER: P3AS05R359740DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1269074
 CATALOG NUMBER: P3AS05R359740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101242
5°	98745
10°	90290
15°	76641
20°	60672
25°	45874
30°	33398
35°	22593
40°	13883
45°	7970
50°	4810
55°	3900
60°	3421
65°	3009
70°	2500
75°	2457
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7970 cd/sqm



TEST NUMBER: P1269074
 CATALOG NUMBER: P3AS05R359740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	13.2
10°-20°	93.1	29.5
20°-30°	87.1	27.6
30°-40°	53.3	16.9
40°-50°	21.0	6.7
50°-60°	9.2	2.9
60°-70°	5.8	1.8
70°-80°	3.1	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.6	70.3
0°-40°	274.9	87.3
0°-60°	305.1	96.9
0°-90°	315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	462	
5°	449	41
15°	338	93
25°	190	87
35°	84	53
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1269074
CATALOG NUMBER: P3AS05R359740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	461.7
1°	462.2
2°	460.8
3°	457.9
4°	453.5
5°	448.6
6°	442.3
7°	435.1
8°	426.3
9°	416.6
10°	405.5
11°	393.8
12°	381.2
13°	367.6
14°	352.6
15°	337.6
17.5°	298.8
20°	260.0
22.5°	222.6
25°	189.6
27.5°	159.1
30°	131.9
32.5°	106.7
35°	84.4
37.5°	64.5
40°	48.5
42.5°	34.9
45°	25.7
47.5°	18.4
50°	14.1
52.5°	11.6
55°	10.2
57.5°	8.7
60°	7.8
62.5°	6.8
65°	5.8
67.5°	4.9
70°	3.9
72.5°	3.4
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.5
85°	1.0
87.5°	0.5



TEST NUMBER: P1269074
CATALOG NUMBER: P3AS05R359740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)