

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269089

Luminaire Tested: P3AS05R409740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 38.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269089

CATALOG NUMBER: P3AS05R409740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269089

CATALOG NUMBER: P3AS05R409740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122578
5°	119018
10°	107992
15°	89217
20°	64359
25°	39801
30°	21548
35°	11136
40°	6069
45°	3380
50°	1706
55°	1262
60°	1140
65°	1090
70°	1090
75°	1017
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3380 cd/sqm

TEST NUMBER: P1269089

CATALOG NUMBER: P3AS05R409740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	18.0
10°-20°	107.0	38.6
20°-30°	76.4	27.6
30°-40°	28.1	10.2
40°-50°	8.9	3.2
50°-60°	3.1	1.1
60°-70°	2.1	0.8
70°-80°	1.3	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.2	84.2
0°-40°	261.4	94.3
0°-60°	273.3	98.7
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	559	
5°	541	50
15°	393	107
25°	164	76
35°	42	28
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1269089

CATALOG NUMBER: P3AS05R409740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	559.0
2.5°	554.7
5°	540.7
7.5°	517.4
10°	485.0
12.5°	443.9
15°	393.0
17.5°	336.0
20°	275.8
22.5°	216.6
25°	164.5
27.5°	120.8
30°	85.1
32.5°	59.7
35°	41.6
37.5°	29.5
40°	21.2
42.5°	15.2
45°	10.9
47.5°	7.4
50°	5.0
52.5°	3.6
55°	3.3
57.5°	3.1
60°	2.6
62.5°	2.4
65°	2.1
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)