

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269120

Luminaire Tested: P3AS05R459740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 206.0 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269120

CATALOG NUMBER: P3AS05R459740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269120

CATALOG NUMBER: P3AS05R459740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43681
5°	42901
10°	40592
15°	37026
20°	32740
25°	28429
30°	24409
35°	20345
40°	15143
45°	9272
50°	4298
55°	3364
60°	3245
65°	2958
70°	2757
75°	2626
80°	2399
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9272 cd/sqm

TEST NUMBER: P1269120

CATALOG NUMBER: P3AS05R459740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	8.8
10°-20°	45.4	22.0
20°-30°	53.9	26.2
30°-40°	46.9	22.8
40°-50°	23.5	11.4
50°-60°	8.2	4.0
60°-70°	5.7	2.8
70°-80°	3.2	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	117.6	57.1
0°-40°	164.4	79.8
0°-60°	196.1	95.2
0°-90°	206.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	206.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	199	
5°	195	18
15°	163	45
25°	118	54
35°	76	47
45°	30	24
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269120

CATALOG NUMBER: P3AS05R459740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	199.2
2.5°	198.2
5°	194.9
7.5°	189.7
10°	182.3
12.5°	173.3
15°	163.1
17.5°	151.7
20°	140.3
22.5°	128.7
25°	117.5
27.5°	106.8
30°	96.4
32.5°	86.4
35°	76.0
37.5°	64.8
40°	52.9
42.5°	41.3
45°	29.9
47.5°	19.7
50°	12.6
52.5°	9.7
55°	8.8
57.5°	8.1
60°	7.4
62.5°	6.6
65°	5.7
67.5°	5.0
70°	4.3
72.5°	3.6
75°	3.1
77.5°	2.4
80°	1.9
82.5°	1.4
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)