

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269144

Luminaire Tested: P3AS05R509740DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509740DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 546.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269144

CATALOG NUMBER: P3AS05R509740DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269144

CATALOG NUMBER: P3AS05R509740DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173846
5°	170328
10°	159538
15°	142839
20°	120200
25°	91723
30°	59604
35°	35335
40°	20438
45°	10234
50°	3821
55°	2982
60°	2763
65°	2542
70°	2500
75°	2457
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10234 cd/sqm

TEST NUMBER: P1269144

CATALOG NUMBER: P3AS05R509740DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	13.2
10°-20°	174.0	31.9
20°-30°	170.7	31.3
30°-40°	86.0	15.7
40°-50°	27.2	5.0
50°-60°	7.1	1.3
60°-70°	5.0	0.9
70°-80°	3.1	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	416.7	76.3
0°-40°	502.7	92.1
0°-60°	536.9	98.3
0°-90°	546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	793	
5°	774	72
15°	629	174
25°	379	171
35°	132	86
45°	33	27
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269144

CATALOG NUMBER: P3AS05R509740DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	792.8
2.5°	787.9
5°	773.8
7.5°	748.6
10°	716.5
12.5°	675.3
15°	629.2
17.5°	575.8
20°	515.1
22.5°	449.5
25°	379.1
27.5°	304.4
30°	235.4
32.5°	177.2
35°	132.0
37.5°	97.6
40°	71.4
42.5°	50.5
45°	33.0
47.5°	18.9
50°	11.2
52.5°	8.3
55°	7.8
57.5°	6.8
60°	6.3
62.5°	5.8
65°	4.9
67.5°	4.4
70°	3.9
72.5°	3.4
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)