

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269149

Luminaire Tested: P3AS05R509740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 208.0 lumens
Efficiency: N/A
Efficacy: 28.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269149
CATALOG NUMBER: P3AS05R509740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269149
 CATALOG NUMBER: P3AS05R509740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42277
5°	41646
10°	39812
15°	36867
20°	33136
25°	29131
30°	24763
35°	20077
40°	15085
45°	9706
50°	4605
55°	3632
60°	3421
65°	3217
70°	2885
75°	2626
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9706 cd/sqm



TEST NUMBER: P1269149
 CATALOG NUMBER: P3AS05R509740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.7	8.5
10°-20°	45.3	21.8
20°-30°	55.0	26.5
30°-40°	46.6	22.4
40°-50°	24.2	11.6
50°-60°	8.7	4.2
60°-70°	6.0	2.9
70°-80°	3.3	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.0	56.7
0°-40°	164.7	79.2
0°-60°	197.6	95.0
0°-90°	208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	208.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	193	
5°	189	18
15°	162	45
25°	120	55
35°	75	47
45°	31	24
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269149

CATALOG NUMBER: P3AS05R509740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	192.8
2.5°	192.1
5°	189.2
7.5°	184.9
10°	178.8
12.5°	170.9
15°	162.4
17.5°	152.6
20°	142.0
22.5°	131.0
25°	120.4
27.5°	109.2
30°	97.8
32.5°	86.4
35°	75.0
37.5°	63.9
40°	52.7
42.5°	42.0
45°	31.3
47.5°	20.9
50°	13.5
52.5°	10.4
55°	9.5
57.5°	8.5
60°	7.8
62.5°	6.9
65°	6.2
67.5°	5.2
70°	4.5
72.5°	3.8
75°	3.1
77.5°	2.4
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)