

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269150

Luminaire Tested: P3AS05R509740DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509740DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 425.0 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269150
CATALOG NUMBER: P3AS05R509740DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1269150
 CATALOG NUMBER: P3AS05R509740DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86375
5°	85098
10°	81339
15°	75324
20°	67696
25°	59495
30°	50590
35°	41037
40°	30829
45°	19847
50°	9415
55°	7417
60°	7017
65°	6538
70°	5898
75°	5338
80°	4925
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19847 cd/sqm



TEST NUMBER: P1269150
 CATALOG NUMBER: P3AS05R509740DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	8.5
10°-20°	92.5	21.8
20°-30°	112.4	26.4
30°-40°	95.3	22.4
40°-50°	49.5	11.6
50°-60°	17.9	4.2
60°-70°	12.4	2.9
70°-80°	6.7	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.1	56.7
0°-40°	336.5	79.2
0°-60°	403.8	95.0
0°-90°	425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	394	
5°	387	36
15°	332	93
25°	246	112
35°	153	95
45°	64	50
55°	19	18
65°	13	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1269150
CATALOG NUMBER: P3AS05R509740DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	393.9
2.5°	392.4
5°	386.6
7.5°	377.9
10°	365.3
12.5°	349.2
15°	331.8
17.5°	311.9
20°	290.1
22.5°	267.8
25°	245.9
27.5°	223.1
30°	199.8
32.5°	176.6
35°	153.3
37.5°	130.5
40°	107.7
42.5°	85.9
45°	64.0
47.5°	42.7
50°	27.6
52.5°	21.3
55°	19.4
57.5°	17.5
60°	16.0
62.5°	14.1
65°	12.6
67.5°	10.7
70°	9.2
72.5°	7.8
75°	6.3
77.5°	4.9
80°	3.9
82.5°	2.9
85°	1.9
87.5°	1.0
90°	0.0

(END OF REPORT)