

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270005

Luminaire Tested: P3AS13R609740DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609740DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 685.0 lumens  
Efficiency: N/A  
Efficacy: 46.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270005  
CATALOG NUMBER: P3AS13R609740DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1270005  
 CATALOG NUMBER: P3AS13R609740DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173605
5°	169711
10°	158870
15°	142543
20°	122581
25°	101353
30°	80088
35°	59481
40°	40962
45°	25677
50°	14123
55°	8296
60°	7412
65°	6330
70°	5450
75°	5592
80°	4799
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25677 cd/sqm



TEST NUMBER: P1270005  
 CATALOG NUMBER: P3AS13R609740DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.8	10.5
10°-20°	174.4	25.5
20°-30°	191.3	27.9
30°-40°	139.4	20.3
40°-50°	65.8	9.6
50°-60°	21.6	3.1
60°-70°	12.2	1.8
70°-80°	6.6	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.4	63.9
0°-40°	576.8	84.2
0°-60°	664.1	97.0
0°-90°	685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	792	
5°	771	72
15°	628	174
25°	419	191
35°	222	139
45°	83	66
55°	22	22
65°	12	12
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1270005  
CATALOG NUMBER: P3AS13R609740DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	791.7
2.5°	787.0
5°	771.0
7.5°	746.5
10°	713.5
12.5°	674.0
15°	627.9
17.5°	578.0
20°	525.3
22.5°	471.6
25°	418.9
27.5°	366.2
30°	316.3
32.5°	268.3
35°	222.2
37.5°	180.7
40°	143.1
42.5°	110.1
45°	82.8
47.5°	60.2
50°	41.4
52.5°	27.3
55°	21.7
57.5°	18.8
60°	16.9
62.5°	14.1
65°	12.2
67.5°	10.4
70°	8.5
72.5°	7.5
75°	6.6
77.5°	4.7
80°	3.8
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)