

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269200

Luminaire Tested: P3AS05R609740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 581.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269200

CATALOG NUMBER: P3AS05R609740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269200

CATALOG NUMBER: P3AS05R609740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152225
5°	143715
10°	139966
15°	136777
20°	127178
25°	113692
30°	86849
35°	50139
40°	19465
45°	8094
50°	1774
55°	268
60°	219
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8094 cd/sqm

TEST NUMBER: P1269200

CATALOG NUMBER: P3AS05R609740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.6	10.6
10°-20°	167.8	28.9
20°-30°	210.2	36.2
30°-40°	117.5	20.2
40°-50°	22.3	3.8
50°-60°	1.1	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.7	75.7
0°-40°	557.2	95.9
0°-60°	580.7	99.9
0°-90°	581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	653	62
15°	602	168
25°	470	210
35°	187	118
45°	26	22
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1269200

CATALOG NUMBER: P3AS05R609740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	694.2
1°	691.4
2°	682.3
3°	671.6
4°	661.7
5°	652.9
6°	646.2
7°	640.5
8°	636.2
9°	632.2
10°	628.6
11°	625.1
12°	621.0
13°	616.0
14°	610.1
15°	602.5
16°	593.2
17°	582.8
18°	570.9
19°	557.3
20°	545.0
21°	531.7
22°	517.9
23°	503.4
24°	487.5
25°	469.9
26°	449.2
27°	426.1
28°	400.2
29°	372.7
30°	343.0
31°	313.0
32°	282.1
32.5°	265.2
33°	250.0
34°	218.4
35°	187.3
36°	159.2
37°	129.5
37.5°	116.0
38°	102.7
39°	82.7
40°	68.0
42.5°	41.4
45°	26.1

TEST NUMBER: P1269200

CATALOG NUMBER: P3AS05R609740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	14.5
50°	5.2
52.5°	1.2
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)