

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270009

Luminaire Tested: P3AS13R659740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1164.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270009

CATALOG NUMBER: P3AS13R659740DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1270009

CATALOG NUMBER: P3AS13R659740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95			94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83			81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77			75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72			70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67			66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63			62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59			58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56			54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284451
5°	267730
10°	264324
15°	259661
20°	245161
25°	227529
30°	176863
35°	102312
40°	41220
45°	18979
50°	7403
55°	2867
60°	2456
65°	2439
70°	2436
75°	2372
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18979 cd/sqm

TEST NUMBER: P1270009

CATALOG NUMBER: P3AS13R659740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.6	9.9
10°-20°	319.4	27.4
20°-30°	418.1	35.9
30°-40°	242.2	20.8
40°-50°	51.8	4.5
50°-60°	8.4	0.7
60°-70°	4.6	0.4
70°-80°	2.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.1	73.3
0°-40°	1095.3	94.1
0°-60°	1155.6	99.3
0°-90°	1164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1216	116
15°	1144	319
25°	940	418
35°	382	242
45°	61	52
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1270009

CATALOG NUMBER: P3AS13R659740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1297.2
2.5°	1260.5
5°	1216.3
7.5°	1198.4
10°	1187.1
12.5°	1171.1
15°	1143.8
17.5°	1101.4
20°	1050.6
22.5°	1002.6
25°	940.4
27.5°	835.9
30°	698.5
32.5°	541.3
35°	382.2
37.5°	241.9
40°	144.0
42.5°	90.4
45°	61.2
47.5°	39.5
50°	21.7
52.5°	10.4
55°	7.5
57.5°	6.6
60°	5.6
62.5°	5.6
65°	4.7
67.5°	3.8
70°	3.8
72.5°	2.8
75°	2.8
77.5°	1.9
80°	1.9
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)