

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269207

Luminaire Tested: P3AS05R609740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 196.0 lumens
Efficiency: N/A
Efficacy: 27.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269207

CATALOG NUMBER: P3AS05R609740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269207

CATALOG NUMBER: P3AS05R609740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34800
5°	34404
10°	33221
15°	31374
20°	28913
25°	26179
30°	23244
35°	19863
40°	15801
45°	11133
50°	6652
55°	3364
60°	3245
65°	2958
70°	2757
75°	2626
80°	2399
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11133 cd/sqm

TEST NUMBER: P1269207

CATALOG NUMBER: P3AS05R609740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.7	7.5
10°-20°	38.6	19.7
20°-30°	49.6	25.3
30°-40°	46.0	23.5
40°-50°	28.0	14.3
50°-60°	9.3	4.8
60°-70°	5.7	2.9
70°-80°	3.2	1.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.9	52.5
0°-40°	148.9	76.0
0°-60°	186.2	95.0
0°-90°	196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	159	
5°	156	15
15°	138	39
25°	108	50
35°	74	46
45°	36	28
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269207

CATALOG NUMBER: P3AS05R609740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	158.7
2.5°	158.0
5°	156.3
7.5°	153.2
10°	149.2
12.5°	144.2
15°	138.2
17.5°	131.3
20°	123.9
22.5°	116.1
25°	108.2
27.5°	100.1
30°	91.8
32.5°	83.5
35°	74.2
37.5°	64.5
40°	55.2
42.5°	45.4
45°	35.9
47.5°	27.8
50°	19.5
52.5°	11.7
55°	8.8
57.5°	8.1
60°	7.4
62.5°	6.4
65°	5.7
67.5°	5.0
70°	4.3
72.5°	3.6
75°	3.1
77.5°	2.4
80°	1.9
82.5°	1.2
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)