

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270031

Luminaire Tested: P3AS13R659740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 320.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270031
CATALOG NUMBER: P3AS13R659740DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1270031
 CATALOG NUMBER: P3AS13R659740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81331
5°	79309
10°	73857
15°	66198
20°	57172
25°	47543
30°	37499
35°	27786
40°	19150
45°	11877
50°	6448
55°	4052
60°	3421
65°	3113
70°	2693
75°	2372
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11877 cd/sqm



TEST NUMBER: P1270031
 CATALOG NUMBER: P3AS13R659740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	10.5
10°-20°	81.0	25.3
20°-30°	89.6	28.0
30°-40°	65.1	20.3
40°-50°	30.5	9.5
50°-60°	10.2	3.2
60°-70°	5.9	1.9
70°-80°	3.1	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.1	63.8
0°-40°	269.2	84.1
0°-60°	309.9	96.9
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	371	
5°	360	33
15°	292	81
25°	196	90
35°	104	65
45°	38	30
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1270031
CATALOG NUMBER: P3AS13R659740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	370.9
2.5°	368.6
5°	360.3
7.5°	347.9
10°	331.7
12.5°	312.8
15°	291.6
17.5°	268.5
20°	245.0
22.5°	220.5
25°	196.5
27.5°	172.1
30°	148.1
32.5°	125.0
35°	103.8
37.5°	84.4
40°	66.9
42.5°	51.2
45°	38.3
47.5°	27.7
50°	18.9
52.5°	12.9
55°	10.6
57.5°	9.2
60°	7.8
62.5°	6.9
65°	6.0
67.5°	5.1
70°	4.2
72.5°	3.7
75°	2.8
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)