

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269218

Luminaire Tested: P3AS05R609740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 353.0 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269218

CATALOG NUMBER: P3AS05R609740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269218

CATALOG NUMBER: P3AS05R609740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89467
5°	87453
10°	81873
15°	73462
20°	63169
25°	52237
30°	41272
35°	30651
40°	21097
45°	13242
50°	7266
55°	4282
60°	3815
65°	3269
70°	2821
75°	2881
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13242 cd/sqm

TEST NUMBER: P1269218

CATALOG NUMBER: P3AS05R609740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.0	10.5
10°-20°	89.9	25.5
20°-30°	98.6	27.9
30°-40°	71.8	20.3
40°-50°	33.9	9.6
50°-60°	11.1	3.1
60°-70°	6.3	1.8
70°-80°	3.4	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.4	63.9
0°-40°	297.2	84.2
0°-60°	342.3	97.0
0°-90°	353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	353.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	408	
5°	397	37
15°	324	90
25°	216	99
35°	114	72
45°	43	34
55°	11	11
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269218

CATALOG NUMBER: P3AS05R609740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	408.0
2.5°	405.5
5°	397.3
7.5°	384.7
10°	367.7
12.5°	347.3
15°	323.6
17.5°	297.9
20°	270.7
22.5°	243.0
25°	215.9
27.5°	188.7
30°	163.0
32.5°	138.3
35°	114.5
37.5°	93.1
40°	73.7
42.5°	56.8
45°	42.7
47.5°	31.0
50°	21.3
52.5°	14.1
55°	11.2
57.5°	9.7
60°	8.7
62.5°	7.3
65°	6.3
67.5°	5.3
70°	4.4
72.5°	3.9
75°	3.4
77.5°	2.4
80°	1.9
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)