

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269295

Luminaire Tested: P3AS09R109740DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109740DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 443.0 lumens
Efficiency: N/A
Efficacy: 35.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269295

CATALOG NUMBER: P3AS09R109740DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269295

CATALOG NUMBER: P3AS09R109740DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111745
5°	108716
10°	99352
15°	87015
20°	74650
25°	62326
30°	49881
35°	37397
40°	27137
45°	17738
50°	11121
55°	7493
60°	6666
65°	6123
70°	5770
75°	5253
80°	4925
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17738 cd/sqm

TEST NUMBER: P1269295

CATALOG NUMBER: P3AS09R109740DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	10.3
10°-20°	106.8	24.1
20°-30°	117.7	26.6
30°-40°	88.1	19.9
40°-50°	45.7	10.3
50°-60°	18.9	4.3
60°-70°	11.7	2.7
70°-80°	6.6	1.5
80°-90°	1.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.1	61.0
0°-40°	358.2	80.8
0°-60°	422.8	95.4
0°-90°	443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	443.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	510	
5°	494	46
15°	383	107
25°	258	118
35°	140	88
45°	57	46
55°	20	19
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1269295

CATALOG NUMBER: P3AS09R109740DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	509.6
1°	510.1
2°	508.5
3°	505.1
4°	500.0
5°	493.9
6°	486.0
7°	477.6
8°	467.5
9°	456.8
10°	446.2
12.5°	415.3
15°	383.3
17.5°	351.3
20°	319.9
22.5°	287.9
25°	257.6
27.5°	227.3
30°	197.0
32.5°	167.2
35°	139.7
37.5°	116.2
40°	94.8
42.5°	75.2
45°	57.2
47.5°	43.2
50°	32.6
52.5°	24.1
55°	19.6
57.5°	17.4
60°	15.2
62.5°	13.5
65°	11.8
67.5°	10.1
70°	9.0
72.5°	7.3
75°	6.2
77.5°	5.1
80°	3.9
82.5°	2.8
85°	1.7
87.5°	0.6
90°	0.0

(END OF REPORT)