

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270083

Luminaire Tested: P3AS17R159740DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270083  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159740DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 983.9 lumens  
Efficiency: N/A  
Efficacy: 46.4 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270083  
CATALOG NUMBER: P3AS17R159740DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270083

CATALOG NUMBER: P3AS17R159740DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65	65	65	65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56	56	56	56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	248204
5°	241470
10°	220659
15°	193281
20°	165798
25°	138443
30°	110777
35°	83092
40°	60313
45°	39446
50°	24664
55°	16668
60°	14780
65°	13594
70°	12759
75°	11607
80°	10986
85°	9309

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39446 cd/sqm



TEST NUMBER: P1270083  
 CATALOG NUMBER: P3AS17R159740DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.2	10.3
10°-20°	237.2	24.1
20°-30°	261.4	26.6
30°-40°	195.7	19.9
40°-50°	101.5	10.3
50°-60°	42.0	4.3
60°-70°	26.0	2.6
70°-80°	14.6	1.5
80°-90°	4.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.8	61.0
0°-40°	795.6	80.9
0°-60°	939.1	95.4
0°-90°	983.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	983.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1132	
5°	1097	101
15°	851	237
25°	572	261
35°	310	196
45°	127	101
55°	44	42
65°	26	26
75°	14	15
85°	4	4
90°	0	



TEST NUMBER: P1270083  
CATALOG NUMBER: P3AS17R159740DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1131.9
1°	1133.1
2°	1129.4
3°	1121.9
4°	1110.7
5°	1097.0
6°	1079.5
7°	1060.8
8°	1038.4
9°	1014.7
10°	991.0
12.5°	922.5
15°	851.4
17.5°	780.4
20°	710.5
22.5°	639.5
25°	572.2
27.5°	504.9
30°	437.5
32.5°	371.5
35°	310.4
37.5°	258.0
40°	210.7
42.5°	167.0
45°	127.2
47.5°	96.0
50°	72.3
52.5°	53.6
55°	43.6
57.5°	38.6
60°	33.7
62.5°	29.9
65°	26.2
67.5°	22.4
70°	19.9
72.5°	16.2
75°	13.7
77.5°	11.2
80°	8.7
82.5°	6.2
85°	3.7
87.5°	1.2
90°	0.0

(END OF REPORT)